# UV photodiode evaluation board hardware manual

V2.0

GaNo Optoelectronics Inc, Suzhou, China

Nov 12, 2018

## **Table of Contents**

1.	Brief description of the UV photodiode evaluation board	3
2.	Interface of the UV photodiode evaluation board	3
3.	Measurement range adjustment of the evaluation board	4


# **Revision History**

Version No.	Date	Revision	Remarks
V1.0	2018-9-19	Draft version	
V2.0	2018-11-12	Revised version 1	

## 1. Brief description of the UV photodiode evaluation board

The UV photodiode evaluation board has both analog and digital output interface. Analog interface provides voltage signal as a function of UV illumination intensity, while digital interface provides serial communication to PC with direct digital output.

The evaluation board supports two types of UV photodiode package. D1 and D2 are used to mount SMD- and TO-type packaged UV photodiodes, respectively. Users could select one of the two mounting ports for UV photodiode evaluation, while both ports can not be supported at the same time. The temperature sensor on board is used for embedded temperature compensation.



#### 2. Interface of the UV photodiode evaluation board

#### 2.1 Analog Interface

P2-1	P2-2	Р3-3
GND	Voltage output signal 0~3.3V	5 V power supply

Note Port P2 provides analog output signal for UV radiation intensity measurement results.

#### **2.2 Digital Interface**

Micro-USB port P1 provides digital interface to PC with USB cable connection. Users could use serial communication host software in PC to receive direct measurement date from the evaluation board. The host software and its operation manual can be downloaded from www.GaNo-OPTO.com.

### 3. Measurement range adjustment of the evaluation board

The evaluation board supports measurement range adjustment function via dip switch S1. Different setting of S1 corresponds to different load resistance value R, which determines the amplification magnitude of the signal processing circuit. The voltage output (0~3.3V) of the evaluation board is V=I× R, where I is the photocurrent from the photodiode under UV illumination.

S1 Dip Switch	Load resistance value	UV radiation intensity @360nm
1 ON, other OFF	10 K	$0.001-0.2 \text{ W/cm}^2$
2 ON, other OFF	100 K	$0.1-20 \text{ mW/cm}^2$
3 ON, other OFF	1 M	$0.01-2 \text{ mW/cm}^2$
4 ON, other OFF	10 M	$0.001-0.2 \text{ mW/cm}^2$

Note The above measurement range is calculated based on a specific photodiode (part. No: GS-ABC-3535LQ). If a different photodiode is used, the measurement range of UV power density will be different.